




CONTACT DIMENSIONS



CONTACT LAYOUT



A2	OBSELETE	Y	A	2	6	1-106012-9
		N		2	3	1-106012-1 A
		Y	A	2	5	106012-9
A2	OBSELETE	N		2	4	106012-4
		N		2	3	106012-1
		CONSERVATION TREATMENT		MATERIAL		PARTNUMBER

1	MATERIAL HOUSING	: GREY GLASSFILLED POLYESTER UL-RATING VØ
	CONTACT	: PHOSPHORBRONZE
2	GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN. AND ACTION PIN: 0,5µm TIN-LEAD MIN.	
3	FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.	
4	CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.	
5	CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.	
6	CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.	
7	CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, UNCONTROLLED ENVIRONMENT APPLICATIONS.	
8	CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE APPROVED LUBRICANT.	
9	CONNECTOR ASSEMBLY WITH LATCH HINGE FOR CABLE CONNECTOR.	
10	CONNECTOR MARKED WITH PARTNUMBER AND DATECODE	
11	PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.	
12	HOLES IN ROW f FOR POSSIBLE FUTURE USE OF GROUND RETURN SHIELDS. (NOT YET TOOLED)	
13	OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN <u>L.v.d.HEIJDEN</u> CHK 15DEC97 <u>D. TRUREN</u> APVD <u>F.v.KONINGSBRUGGE</u> PRODUCT SPEC APPLICATION SPEC 114-19029 WEIGHT —		 Tyco Electronics Corporation s-Hertogenbosch, Netherlands,	
DIMENSIONS: MM 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME Z-PACK 2MM HM TYPE C 55 POS. RIGHT ANGLE MALE CONNECTOR ASSEMBLY SIZE A2	
MATERIAL —		FINISH —		CAGE CODE 00779 DRAWING NO C-106012 RESTRICTED TO —	
CUSTOMER DRAWING				SCALE	NTS
				SHEET	1 OF 1
				REV	12