

PRODUCT NUMBER


71600-YXXLF

LEAD FREE, SEE NOTE 6

TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2


OPTIONAL STRAIN RELIEF
SEE SHEET 2

TRIANGLE INDICATES
POSITION 1
NOTE 5



NOTES:

- 1 - PLASTIC MAT'L : GLASS FILLED HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: GREY
- 2 - PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PRODUCT PACKAGED IN TUBES.
- 4 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- 5 - 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.
- 2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO LEFT AND RIGHT POLARIZING SLOT.
- 2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT POLARIZING SLOT.
- 2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT
- 2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT
- 6 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.
PACKAGING SPECIFICATION AS PER GS-14-920.



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family 2.54MM IDC
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
AP	F12-0046	LMU	12.04.25	angles	X.X ±0.3		QUICKIE III FEM
AR	B-17851	LMU	14.06.05	linear	X.XX ±0.13		0.76µm Au
					X.XXX ±0.05	scale 5:1	
AK	F05-0180	LMU	05.04.22	dr	D.LE	01.01.24	dwg no
AL	F06-0270	LMU	06.09.12	engr	P.NZ	01.01.24	sheet 1 of 2
AM	F06-0274	LMU	06.09.25	chr	JF.N	01.01.24	size
AN	F09-0233	LMU	09.12.15	appd	P.NZ	01.01.24	A3
sheet	revision	AR	AF				type
index	sheet	1	2				CUSTOMER Drawing



Copyright FCI

STRAIN RELIEF OPTION AVAILABILITY		Nbr OF POSITIONS	
1/6	04		
0/1/2/3/6	06		
0/1/2/3/6	08		
0/1/2/3/6	10		
0/1/2/3/6	14		
0/1/2/3/6	16		
0/1/2/3/6	18		
0/1/2/3/6	20		
0/1/3	24		
0/1/2/3/6	26		
0/1/2/3/6	30		
0/1/2/3/6	34		
0/1/2/3/6	40		
0/1/2/3/6	50		
0/1/2/3/6	60		
0/1/2/3/6	64		

624
304
204 / 224
004

DASHES NOT AVAILABLE

PLATING
0.76µm GOLD ON CONTACT AREA
1.27 µm Ni REMAINDER OF PRODUCT

(Nx2.54+4.47)-0.08

LOW PROFILE STRAIN RELIEF

(Nx2.54+4.47)-0.08

STANDARD STRAIN RELIEF

(Nx2.54+4.47)-0.08

5.5 MAX

LATCHING STRAIN RELIEF FOR SLIM HEADER

WITHOUT STRAIN RELIEF

WITH LOW PROFILE STRAIN RELIEF

WITH STANDARD STRAIN RELIEF

WITH LATCHING STRAIN RELIEF

PRODUCT NUMBER	WITH CENTRAL KEY	WITHOUT STANDARD	WITHOUT LOW PROFILE	LATCHING
71600-6YYLF	●			●
71600-3YYLF		●	●	
71600-2YYLF	●			●
71600-1YYLF	●		●	
71600-0YYLF	●	●		

mat'l. code				surface			tolerance			projection		product family		
ltr	ecn no	dr	date	ISO 1302	ISO 406	ISO 1101	tolerances unless otherwise specified			mm		QUICKIE		
AF	B-17851	LMU	14.06.05	angles								title		
AA	F10199	GCO	01.04.26	linear						scale N/A		IDC RECEPT DR		
AB	F03019	DLE	03.01.23	dr	D.LE	01.01.24						sheet 2 of - size		
AC	F05-0180	LMU	05.04.22	engr	P.NZ	01.01.24						A3		
AD	F06-0270	LMU	06.09.12	chr	JF.N	01.01.24						dwg no		
AE	F06-0274	LMU	06.09.25	appd	P.NZ	01.01.24						71600		
sheet index				revision sheet						type			CUSTOMER Drawing	