


LOC		DIST							REVISIONS			
DF	ZO		P	F	ZONE	LTR			DESCRIPTION	DATE	APPD	
						F			REV PER 063D-0408-00	CT	1-01	DN

1. QUALITY CONFORMANCE INSPECTION PER MIL-C-55302 (GROUP A, B & C).
2. PACKAGED PER MIL-C-55302
- 3 THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY, NOT TO CONTACT LOCATIONS.
- 4 SLOT OPTIONAL AT INDICATED AREA OF HOUSING.
- 5 CONTACTS: GOLD FLASH OVER 0.000762 TO 0.00381 [0.000030 TO .000150] NICKEL ENTIRE CONTACT, 0.00127[0.000050] GOLD ON CONTACT AREA ONLY.
- 6 TOLERANCE TO CENTER OR RADIUS IS ± 0.15 [.006], TO END OF BLOCK ± 0.51 [.020].
- 7 MARKED IN APPROXIMATE AREA SHOWN
EXAMPLE: AMP PART NO
 DATE CODE MILITARY PART NUMBER
- 8 CHARACTERS MARKED IN AREA SHOWN, EVERY FIFTH POSITION MARKED WITH A BAR
9. "CSA" LOGO MARKED ON HOUSING.



M55302/128-DL2A	158.95 [6.258]	59	120	1-102192-1
M55302/128-DA2A	133.55 [5.258]	49	100	1-102192-0
M55302/128-CG2A	108.15 [4.258]	39	80	102192-9
M55302/128-BH2A	70.05 [2.758]	24	50	102192-8
M55302/128-DB2A	136.09 [5.358]	50	102	102192-7
M55302/128-AM2A	39.57 [1.558]	12	26	102192-6
M55302/128-AK2A	34.49 [1.358]	10	22	102192-5
M55302/128-BN2A	82.75 [3.258]	29	60	102192-4
M55302/128-BK2A	75.13 [2.958]	26	54	102192-3
M55302/128-BM2A	80.21 [3.158]	28	58	102192-2
M55302/128-CJ2A	113.23 [4.458]	41	84	102192-1
MILITARY PART NUMBER	B	A	NO OF POSN	PART NUMBER

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC $\pm$ 0 3 PLC DEC $\pm$ 0.25[.010] ANGLES $\pm$ -		DR 5-1-91 J GALLUCCI BG	AMP AMP Incorporated Harrisburg, PA 17105-3608	
MATERIAL HOUSING: POLYPHENYLENE SULFIDE, NATURAL CONTACTS: PH BRZ FINISH		CHK 6-10-91 KATE HELM APPD 6-10-91 DIRK DIXON APPD 6-10-91 DIRK DIXON PRODUCT SPEC APPLICATION SPEC WEIGHT -		
			NAME	
			ASSEMBLY, HOUSING, MOD II, 2.54[.100] DOUBLE ROW, WITH GUIDE PIN EARS, SHORT POINT CONTACTS	
			SIZE D	CAGE CODE 00779
			DRAWING NO 102192	
			SCALE 5:1	SHEET 1 OF 1