



UNIT:mm




CABLE WHITE PRINT
HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+28AWG/2C
E189529 AWM STYLE 2725 80°C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V



⑦ PE BAG				1/5	CLEAR SIZE: 330*380*0.05mm PRINT BLACK"MADE IN CHINA"+5PCS"及印生产周期, 有透气孔.		Industrial Cable and Connector Technology DRAWN ZHONGHS DRAWING NO CHECKED CUSTOMER APPROVAL ITEM NO. 102-1031-BL-00500 DECIDED DATE 2012-02-16 VERSIONS/EDITION A/0 PROJECTION 
⑥ PE BAG				1	CLEAR SIZE: 210*250*0.05mm PRINT BLACK"MADE IN CHINA"+1PC"及印生产周期, 有透气孔.		
⑤ TIE				1	BLACK L=80mm		
④ OUT JACKET				12g	BLACK PVC-50P (MOULD NO:WM-40 & WM-88)		
③ CABLE				1	BLACK USB2.0 UL2725 28#/1P+28#/2C+AEB OD:3.8mm L=5000±15		
② CONN				1set	USB2.0 刺破式 ATYPE MALE SHELL:NICKEL PIN:G/F 4PCS TYPE INSULATOR COLOR:WHITE		
① CONN				1set	USB2.0 刺破式 MINI 5P MALE SHELL:NICKEL PIN:G/F 3PCS INSULATOR COLOR:BLACK		
NO.				NAME	Q'TY	SPECIFICATION	