






- 1 ZINC PER ASTM B 86.
- 2 BERYLLIUM COPPER PER ASTM B 196.
- 3 POLYMETHYLPENTENE, BLUE, GENERAL PURPOSE.
- 4 TIN PLATE PER ASTM B 545
3.81 μ m [.000180] MINIMUM THICK.
- 5 TIN PLATE PER ASTM B 545
2.54 μ m [.000100] MINIMUM THICK.
- 6 SILVER PLATE PER ASTM B 700
5.08 μ m [.000200] MINIMUM THICK.
- 7. CONNECTOR WILL ACCEPT CENTER CONDUCTOR
DIAMETER RANGE OF 0.97[.038]-1.65[.065].
- 8 MAJOR DIAMETER MODIFIED TO .363 REF.



SCALE 4:1
RECOMMENDED PANEL CUTOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. HAVENER	08DEC2005	tyco <i>Electronics</i> Tyco Electronics Corporation Harrisburg, PA 17105-3608		NAME JACK, 15 AMP, PCB, G SERIES					
		CHK K. WEIDNER	08DEC2005								
DIMENSIONS: mm [INCHES]		APVD K. WEIDNER	08DEC2005								
		PRODUCT SPEC —									
		APPLICATION SPEC —									
		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO						
MATERIAL SEE NOTES 1-3		WEIGHT —		A2	00779	C=5415332	—				
		CUSTOMER DRAWING				SCALE	10:1	SHEET	1 of 1	REV	0
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH									