

Specification

Model Name : AC 0212A




Input Voltage	100 ~ 240 Vac
Input Frequency	47 ~ 63Hz
Max. In-rush Current	Cold start , 15A for 115Vac , 30A for 230Vac
Input Current	1.6A Max for 115Vac 0.8A Max for 230Vac
Output Voltage	14.6Vdc 13.7Vdc
Max. Charging Current	2A
Working Temperature	0 ~ 50 Degree C
Hold up time	8 ms at full load output power and 115Vac input
LED Indication	LED1 : RED LED → CHARGING LED2 : GREEN LED → FULL CHARGE
Dimensions	4.68 inch (119 mm) Length 2.36 inch (60 mm) Width 1.34 inch (34 mm) Height



IDEAL POWER
IDEAL POWER SOLUTIONS

Charging Curve :



Case Drawing

Body View



Ideal Power, Acorn House, Tree Beech Enterprise Park, Gunn, Barnstaple, Devon, England EX32 7NZ

Web. www.idealpower.co.uk

Tel. +44 (0) 845 2603400

email. sales@idealpower.co.uk

Fax. +44 (0) 845 2603401

Front Panel



Rear Panel

