

F57 UK Desktop Unregulated 20 Watts Series

Features

- 230 VAC Input
- Desktop Style
- Rated for Continuous Duty
- Filtered
- Unregulated Outputs up to 20 Watts
- Safety Agency Approved/CE Compliant
- Impact Resistant Polycarbonate Enclosure
- Private Label Marking Available
- 1 Year Warranty
- Modified and Custom Designs Also Available
- Manufactured in China

Ault Model	Rated Output Volts DC	Output Current-Amps	Maximum Watts
F57-102000-K000G	10	2.00	20.0
F57-111818-K000G	11	1.82	20.0
F57-121667-K000G	12	1.67	20.0
F57-141429-K000G	14	1.43	20.0
F57-151333-K000G	15	1.33	20.0
F57-181111-K000G	18	1.11	20.0
F57-201000-K000G	20	1.00	20.0
F57-210952-K000G	21	0.95	20.0
F57-220909-K000G	22	0.91	20.0
F57-240833-K000G	24	0.83	20.0

Input

- Voltage 230 VAC
- Line Frequency 50 Hz
- Connector UK Input Cord

Electrical

- Topology DC Unregulated Power Supply
- Dielectric Withstand 3000 VAC primary-secondary
- Protection Current, Thermal or Energy Limiting
- EMI Complies with EMC Directives
- CE CE Compliant

Safety Approvals

EN60950

Environmental

- Operating Temperature 0° to 40° C with no derating
- Storage Temperature -30° to +85° C
- Relative Humidity 5% to 95% non-condensing
- Altitude 0-10,000 feet
- Cooling Convectional – non vented case

Mechanical

- Case Dimensions F57 - UK Dual Cord
3.5 L x 2.7 W x 2.1 H (in)
88 L x 68 W x 54 H (mm)
- Case Material Black 94 V1 Polycarbonate
- Weight 24 ounces, 695 grams,
(excluding cord)
- Input Cord and Connector 6 ft., 2 Conductor, 18 AWG, with
2-Prong North American Plug
- Output Cord and Connector 6 ft., 2 Conductor, 24 AWG
Ault #3 Connector
Other Connectors Available

ONE YEAR WARRANTY

Ault Incorporated, 7105 Northland Terrace, Minneapolis, MN 55428

Contact Ault Inc. for all your custom design requirements. Phone: 763.592.1900 · Fax: 763.592.1911