



Wiha. Premium Tools
for Professionals.

Wiha PicoFinish. The Specialist for Precision Applications.



The soft material of the handle, together with the rotating cap, enables optimum and sensitive twisting.



The clear marking of the drive on the rotating cap provides easy and fast identification of the required screwdriver.




The Wiha PicoFinish screwdrivers are predestined for high-precision work, predominantly with electro-technical and precision components.

The octagonal rapid-rotation zone at the front of the handle allows rapid twisting.

The extraordinarily easy-to-twist rotating cap permits the delicate turning of fine screws with just one hand.

PicoFinish Advantages:

- Special soft plastic material assures comfortable, delicate work
- Ideal for fine adjustments in electronic assembly work and precision applications, as well as for hobby use and model making
- Clear marking of the drive on the rotating cap provides easy and fast identification of the required screwdriver
- Convex handle end allows the transmission of a controlled high torque to powerfully tighten or loosen the screw head
- Palm saving rotating cap with a large surface for the fingers makes incremental adjustment easy
- Wiha ChromeTop-finish on tip for a perfect fit every time





Wiha. Premium Tools
for Professionals.

Wiha PicoFinish. The Specialist for Precision Applications.

For Hexagon Socket Screws.



263 P Hex Screwdriver.

With rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.	Hex	Cap	Shank	Tip	Length
00519 1	0.7	40	140	18	10
00520 7	0.9	40	140	18	10
00521 4	1.3	40	140	18	10
00522 1	1.5	50	150	18	10
00523 8	2	50	150	18	10
00524 5	2.5	60	160	18	10
00525 2	3	60	160	18	10

263 P Inch Hex Screwdriver.

With rotating cap and rapid-turning zone. Inch sizes.

Order-No.	Hex	Cap	Shank	Tip	Length
00519 1	0.028"	40	140	18	10
00520 7	0.035"	40	140	18	10
00521 4	0.050"	40	140	18	10
00526 9	1/16"	50	150	18	10
00523 8	5/64"	50	150	18	10
00528 3	3/32"	60	150	18	10
00530 6	7/64"	60	150	18	10
00527 6	1/8"	60	150	18	10

For Hexagon Socket Screws.



264 P Ballpoint Hex Screwdriver.

With rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Extra: Ballpoint allows up to 25 degree entry angle to fastener.

Order-No.	Hex	Cap	Shank	Tip	Length	Part No.
00531 3	1.3	40	140	18	10	310-6159
00532 0	1.5	50	150	18	10	310-6160
00533 7	2	50	150	18	10	310-6172
00534 4	2.5	60	160	18	10	310-6184
00535 1	3	60	160	18	10	310-6196

264 P Inch Ballpoint Hex Screwdriver.

With rotating cap and rapid-turning zone. Inch sizes.

Order-No.	Hex	Cap	Shank	Tip	Length
00531 5	0.050"	40	120	18	10
00537 5	1/16"	50	150	18	10
00541 2	5/64"	50	150	18	10
00539 9	3/32"	50	150	18	10
00542 9	7/64"	60	160	18	10
00538 2	1/8"	60	160	18	10
00543 6	9/64"	60	160	18	10
00540 5	5/32"	60	160	18	10