




STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (METER)
X-0233889-Y	XY,0

- NOTES:
1. INSERTION LOSS $\leq 0,5$ dB, MEASURED AGAINST REF. CONNECTOR.
 2. RETURN LOSS ≥ 65 dB, MATED
 - $\triangle$ APC ANGLE = 8° (SC/APC AND FC/APC)
 4. CABLE:
 - 9/125 μm
 - DIAMETER: 3,0 mm
 - COLOUR: YELLOW
 - TIGHT BUFFER
 - OUTER SHEATH MATERIAL: PVC
 - $\triangle$ INFO ON CABLE LABEL:
 - TYCO PART NUMBER
 - P.O. NUMBER AND PROD. DATE (FORMAT YYWW)
- EXAMPLE:

TYCO 0-0233889-2
0-1234-5 0204

L	—	CABLE $\varnothing$ 3,0 mm	15
2	—	CABLE LABEL	14
1	—	FC CAP PROTECTIVE, WITH STRAP, BLACK	13
1	—	FC COUPLING NUT	12
1	—	FC PLUG BODY	11
1	—	FERR. SUBASSY SM 0,126/1,1	10
1	—	INTERNAL BODY FC	9
1	—	CAP PROTECTIVE, WITH STRAP, BLACK	8
2	—	STRAIN RELIEF PUSH ON GREEN	7
2	—	CRIMP EYELET	6
1	—	INTERNAL BODY SC, 3 mm	5
2	—	SPRING COMPRESSION, 3 mm	4
1	—	FERR. SUBASSY	3
1	—	PLUG BODY SC, GREY	2
1	—	CONN. HOUSING AMP SC1, GREEN	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL
—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	$\pm$ —
1 PLC	$\pm$ —
2 PLC	$\pm$ —
3 PLC	$\pm$ —
4 PLC	$\pm$ —
ANGLES	$\pm$ —
FINISH	—

DWN
R.COOLEN
29 JAN 02

CHK
R.MAARTENS
29 JAN 02

APVD
R.MAARTENS
29 JAN 02

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics Corporation
's-Hertogenbosch Nederland

FOSM LEAD 3,0
SC/APC — FC/APC

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-233889

RESTRICTED TO
—

SCALE
—:—

SHEET
1 OF 1

REV
A