

LAMINATED TRANSFORMERS

Type EI60 / 25.5 - 25VA




AGENCY APPROVALS **CE**

3. EN61558



- Frequency 50/60Hz
- Potted under vacuum
- Split-bobbin
- Temperature class t_a 40°C/B
- Weight: 0.67kg
- Packaging unit: 6 pieces (tray)


Mechanical



***NOTE:** When checking the approval status of this product with VDE, add the prefix "BV" to the orderable Part Number (these letters will also be found on the part label). **The prefix is not part of the orderable Part Number.**

Primary (V)	Secondary (V / mA)	No-Load Voltage (V)	Schematic No.	Part Number	Agency Approvals
230	6 / 4170	6.90	1	060-0201.0	3*
230	9 / 2780	10.30	1	060-0202.0	3*
230	12 / 2080	13.60	1	060-0203.0	3*
230	15 / 1670	17.00	1	060-0204.0	3*
230	18 / 1390	20.50	1	060-0205.0	3*
230	24 / 1040	27.00	1	060-0206.0	3*
230	2x6 / 2080	2x6.90	2	060-0207.0	3*
230	2x9 / 1390	2x10.50	2	060-0208.0	3*
230	2x12 / 1040	2x13.60	2	060-0209.0	3*
230	2x15 / 830	2x17.30	2	060-0210.0	3*
2x115	6 / 4170	6.90	3	060-0272.0	3*
2x115	9 / 2780	10.30	3	060-0273.0	3*
2x115	12 / 2080	13.60	3	060-0274.0	3*
2x115	15 / 1670	17.00	3	060-0275.0	3*
2x115	18 / 1390	20.50	3	060-0276.0	3*
2x115	24 / 1040	27.00	3	060-0277.0	3*
2x115	2x6 / 2080	2x6.90	4	060-0278.0	3*
2x115	2x9 / 1390	2x10.50	4	060-0279.0	3*
2x115	2x12 / 1040	2x13.60	4	060-0280.0	3*
2x115	2x15 / 830	2x17.30	4	060-0281.0	3*

Schematics



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[060-0201-0](#) [060-0202-0](#) [060-0203-0](#) [060-0204-0](#) [060-0205-0](#) [060-0206-0](#) [060-0207-0](#) [060-0208-0](#) [060-0209-0](#)
[060-0210-0](#) [060-0272-0](#) [060-0273-0](#) [060-0274-0](#) [060-0275-0](#) [060-0276-0](#) [060-0277-0](#) [060-0278-0](#) [060-0279-0](#)
[060-0280-0](#) [060-0281-0](#)