



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


ALL INTERNATIONAL RIGHTS RESERVED.

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.

LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
FT	0		L	REVISED PER ECO-10-021995	12JAN11	HMR	MG	



ALTERNATE POSITION FOR
90° CABLE CLAMP



- BRACKET & U BOLT: STAINLESS STEEL.
CABLE CLAMP AND HEX NUTS: CARBON STEEL.
PROTECTIVE SLEEVES: POLYVINYL CHLORIDE.
- BRACKET & U BOLT: PASSIVATED.
CABLE CLAMP: 5.08um[.000200] MIN NICKEL.

SUPERSEDED BY 201848-5	201848-5
	201848-1
PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.REIFSNYDER 31 OCT 95	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK R.STONE 02 NOV 95				
DIMENSIONS: mm [INCHES]		APVD G.A.STEINHAUER 02 NOV 95	NAME			
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.38[.015] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -	PRODUCT SPEC			
			APPLICATION SPEC			
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-	A2	00779	C=201848	-
CUSTOMER DRAWING			SCALE	2:1	SHEET	1 OF 1
			REV			
			L			