





Copyright FCI.



Part Number & Date Code Printing

PC card drilling dimensions(after plating)
(thickness 1.60 $\pm$ 0.20mm)



Pull parts						
SHELL	A ± 0.38	B ± 0.12	C ± 0.10	D ± 0.25	E ± 0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S33E4GX00**
15	39.14	33.32	25.18	24.54	19.18	D15S33E4GX00**
25	53.03	47.04	39.12	38.25	33.12	D25S33E4GX00**

GENERAL CHARACTERISTICS : SEE DRAWING C01-8546-0000

LF FOR LEAD FREE

European Views

rev	ecn no	dr	date
E	105-0124	JS	2005/07/27
F	106-0074	SK	2006/06/08
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JOHN SLEEBA	1994/10/14	ANGULAR LINEAR	0.X		±0.1		size A3	Scale 1:1	
Eng	GEORGE VJ	1994/10/14		0.XX		±0.1				
Chr	GEORGE VJ	2005/07/27		0.XX	±1°	0.XXX			±0.1	
Appr	KVSD	2005/07/27	Product family				D-SUB		Spec ref -	
			title SOCKET CONNECT.DELTA D RIGHT ANGLE WITH NUT, HARPOON AND METAL PLATE				no C-8646-00146-2		Rev. F	
			catalog no DELTA-D				CUSTOMER		sheet 1 of 1	

REV F - 2006-04-17