





UNIT:mm



P1	P2
1	1
2	2
3	3
4	4
SHEEL	SHEEL

Electronic Test:
1.100% Test,(Open,Short,Miss Wire)
2.Contact Resistance:3 ohm max.
3.Insulation Resistance:20M ohm min.
4.Hi-Pot:300V DC/10ms



⑤	PE BAG	1/10	CLEAR SIZE:170*250*0.05mm PRINT BLACK"MADE IN CHINA"+10PCS"及印生产周期,有透气孔.
④	PE BAG	1	CLEAR SIZE: 80*100*0.05mm PRINT BLACK"MADE IN CHINA"+1PC"及印生产周期,有透气孔.
③	OUT JACKET	6g	BEIGE(V-29) 40P PVC(MOULD NO:WM-005)
	IN JACKET	4g	CLEAR LDPE.
②	CABLE	4	28AWG 电子线, L=30MM
①	CONN	2	USB A FEMALE,SHELL NICKEL PIN GOLD FLASH SHORT BODY
NO.	NAME	Q'TY	SPECIFICATION
4			

Cnc Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY	ZHONGHS	DRAWING NO.	
CHECKED BY		CUSTOMER	
APPROVAL BY		ITEM NO.	421-AF-AF
DECIDE BY		DATE	2012-02-27
VERSIONS/EDITION	A/0	PROJECTION	—  —