

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982680108](#)
Status: **Active**
Overview: [Premo-Flex Cable Jumpers](#)
Description: 1.25mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 102.00mm Cable Length, Tin (Sn) Plating, 6 Circuits

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Packaging Specification PK-98268-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Cable
 Series [98268](#)
 Comments Contacts on opposite sides, Type D
 Crimp Quality Equipment Yes
 Overview [Premo-Flex Cable Jumpers](#)
 Product Name Premo-Flex FFC Jumper
 UPC 756054773536

Physical

Cable Length 102.00mm
 Circuits (Loaded) 6
 Material - Plating Mating Tin
 Net Weight 0.552/g
 Packaging Type Bag
 Pitch - Mating Interface 1.25mm
 Temperature Range - Operating -40° to +105°C
 Wire Size AWG N/A
 Wire/Cable Type Flat Flex Cable


Electrical

Current - Maximum per Contact 1.4A
 Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification PK-98268-001-001
 Sales Drawing SD-98268-001



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[98268 Series](#)

Mates With

Molex FFC – FPC connector. Be sure to match like plating.