


Boots

13AC141, 13AC142

KOBICONN

Boots



Dimensions: In.

SPECIFICATIONS

Material:	.039 $\pm$.012" Thick Vinyl Chloride
Withstand Voltage:	2000VAC for 1 Minute
Insulation Resistance:	$\geq 100\text{M}\Omega$ @ 500VDC
Withstand Temperature:	-30°C ~ +100°C for 10 hrs. Minimum
Tensile Strength:	1.2~1.5kg/mm ²
Color:	13AC141- Red, 13AC142- Black

Date Last Revised: 10-19-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300799

13AC141, 13AC142

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[13AC142](#) [13AC141](#)