



preci-dip

## PCB CONNECTORS - RIGHT ANGLE SOLDER TAIL

Series: PCB Connectors - Right angle solder tail  
852: Double row  
1.27 mm, Right angle solder tail

Ultraminiature PCB pin connectors, solder tail, right angle.

### Technical specs.:

Insulator: Black glass filled polyester  
PCT-GF30-FR  
Flammability: UL 94V-O  
Contact: Brass CuZn36Pb3 (C36000)  
Connecting pin Ø: 0.41 mm  
Mechanical life: Min. 500 cycles  
Rated current: 1 A  
Dielectric strength: Min. 1000 V RMS




### Ordering information RoHS-compliant parts

| PP Plating code | Termination  | Connecting pin |
|-----------------|--------------|----------------|
| 10              | Gold 0.25 µm | Gold 0.25 µm   |
| 80              | Tin          | Tin            |

**NNN number of poles.** Replace **NNN** with the requested number of poles, e.g. 852-10-**NNN**-20-001101 for a double row version with 16 pins becomes 852-10-**016**-20-001101.

General technical specs. ...

### 852-PP-NNN-20-001101



Right angle pin connector: solder tail, double row.

Availability from: 4 to 100 contacts.  
Standard number of contacts 50 and 100.