

SKINTOP® SL/ SLR


Liquid Tight, Non-Metallic Strain Relief Cable Gland with PG Threads



SKINTOP® SL/ SLR is a durable, liquid tight, easy to assemble strain relief cable gland with PG threads that is universally suited for all types of machinery & equipment, including automation, motion control, process control and robotics.

Application Advantage:

- The heavy duty SKINTOP® design provides great pullout strength and very reliable strain relief
- Superior integrated locking mechanism includes an internal ratchet for vibration proof protection
- Multi-trapezoidal thread requires just one twist to tighten
- Generous high quality neoprene bushing provides a liquid tight and dust proof, hermetic seal



NOTES:

1. Orders of 2000 pieces or more per item will be bulk packaged unless otherwise requested.
2. UL Status: R = Recognized; L = Listed

Complete the installation with:



Technical Data:

	Materials:			Color:	Black (RAL 9005) UV Resistant Gray (RAL 7001)
	Body:	Polyamide			
	Bushing:	CR			
	Locknuts:	Included		IP Protection:	70 PSI IP 68, 5 Bar (Exceeds NEMA 6/ 6P Pressure rating)
				Seal:	
	Static:	-40°C to +80°C			
	Dynamic:	-20°C to +80°C			

SKINTOP® SL: Liquid Tight, Non-Metallic Strain Relief Cable Gland with PG Threads

Black	Part Number	Gray	Thread Type & Size	UL Status	Clamping Range ØF inches	SW Wrenching Flats inches	C Overall Length inches	D Thread Length inches	Standard Pack Size	Weight 100 pcs. lbs.
	S2107	S1107	PG-7	R	0.098 - 0.256	0.591	1.260	.315	100	1.00
	S2109	S1109	PG-9	R	0.138 - 0.315	0.748	1.417	.315	100	1.50
	S2111	S1111	PG-11	R	0.157 - 0.394	0.866	1.496	.315	100	2.00
	S2113	S1113	PG-13	L	0.236 - 0.472	0.945	1.614	.354	100	2.50
	S2116	S1116	PG-16	L	0.354 - 0.551	1.063	1.732	.394	50	3.00
	S2121	S1121	PG-21	L	0.512 - 0.709	1.299	1.929	.433	50	5.00
	S2129	S1129	PG-29	R	0.551 - 0.984	1.654	2.205	.433	25	8.50
	S2136	S1136	PG-36	L	0.945 - 1.260	2.087	2.598	.512	10	17.50
	S2142	S1142	PG-42	R	1.378 - 1.496	2.362	2.677	.512	5	24.00
	S2148	S1148	PG-48	L	1.535 - 1.732	2.559	2.717	.551	5	29.00

SKINTOP® SLR: Liquid Tight, Non-Metallic Strain Relief Cable Gland with Reducer Bushing

Black	Part Number	Gray	Thread Type & Size	UL Status	Clamping Range ØF inches	SW Wrenching Flats inches	C Overall Length inches	D Thread Length inches	Standard Pack Size	Weight 100 pcs. lbs.
	S2207	S1207	PG-7	R	0.059 - 0.197	0.591	1.260	.315	100	1.00
	S2209	S1209	PG-9	R	0.079 - 0.236	0.748	1.417	.315	100	1.50
	S2211	S1211	PG-11	R	0.079 - 0.276	0.866	1.496	.315	100	2.00
	S2213	S1213	PG-13	L	0.157 - 0.354	0.945	1.614	.354	100	2.50
	S2216	S1216	PG-16	L	0.236 - 0.472	1.063	1.732	.394	50	3.00
	S2221	S1221	PG-21	L	0.354 - 0.630	1.299	1.929	.433	50	5.00
	S2229	S1229	PG-29	R	0.433 - 0.787	1.654	2.205	.433	25	8.50
	S2236	S1236	PG-36	L	0.669 - 1.024	2.087	2.598	.512	10	17.50
	S2242	S1242	PG-42	R	0.866 - 1.220	2.362	2.677	.512	5	24.00
	S2248	S1248	PG-48	L	1.024 - 1.378	2.559	2.717	.551	5	29.00