




Cable Types		
	RG213/U	RG214/U (Double Shield)
Model	1658-S-XX	1658-T-XX
Capacitance pf/ft	30.8	30.8
Nominal Impedance	50	50
Cable Diameter	Ø .405	Ø .425

MATERIALS:

Conn:1st end – Type "N" Male, See table above.

Finish: Body and Fitting, Tarnish resistant.

Center contact: Gold plated per requirement of MIL-C-39012.

Nominal Impedance: 50 Ohms.

Cable: See table above. Marking: "POMONA 1658-X-XX".

Conn:2nd end – Same as first end.

RATINGS:

Operating Voltage: 1000 VRMS Max.

Operating Temperature: +89°C Max.

ORDERING INFORMATION: Model 1658-X-XX

XX = Cable Lengths, Standard Length: 18" (457), 24" (610), 36" (914), 48" (1219) & 60" (1542).

Additional lengths can be quoted upon request.

Ordering Example: 1658-T-24 Indicates 24" in length

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA