

Plastic

POWER	500 mW	1 W	5 W
PACKAGE	DO-7	DO-41	Case 17
Zener Volts			
68	1N5266 B	1N4760 A	1N5373 B
75	1N5267 B	1N4761 A	1N5374 B
82	1N5268 B	1N4762 A	1N5375 B
87	1N5269 B		1N5376 B
91	1N5270 B	1N4763 A	1N5377 B
100	1N5271 B	1N4764 A	1N5378 B
110	1N5272 B		1N5379 B
120	1N5273 B		1N5380 B
130	1N5274 B		1N5381 B
140	1N5275 B		1N5382 B
150	1N5276 B		1N5383 B
160	1N5277 B		1N5384 B
170	1N5278 B		1N5385 B
180	1N5279 B		1N5386 B
190	1N5280 B		1N5387 B
200	1N5281 B		1N5388 B

Glass

Note: All the above preferred types have 50/o tolerance.

POWER	400 mW	400 mW	500 mW	1.5 W
PACKAGE	DO-7		DO-35	DO-41
Zener Volts				
2.4	1N4370 A		BZX79C2V4	
2.5				
2.7	1N4371 A		BZX79C2V7	
2.8				
3.0	1N4372 A		BZX79C3V0	
3.3	1N746 A		BZX79C3V3	1N5913 B
3.6	1N747 A		BZX79C3V6	1N5914 B
3.9	1N748 A		BZX79C3V9	1N5915 B
4.3	1N749 A		BZX79C4V3	1N5916 B
4.7	1N750 A		BZX79C4V7	1N5917 B
5.1	1N751 A		BZX79C5V1	1N5918 B
5.6	1N752 A		BZX79C5V6	1N5919 B
6.0				
6.2	1N753 A		BZX79C6V2	1N5920 B
6.8	1N754 A	1N957 B	BZX79C6V8	1N5921 B
7.5	1N755 A	1N958 B	BZX79C7V5	1N5922 B
8.2	1N756 A	1N959 B	BZX79C7V2	1N5923 B
8.7				
9.1	1N757 A	1N960 B	BZX79C9V1	1N5924 B
10	1N758 A	1N961 B	BZX79C10	1N5925 B
11		1N962 B	BZX79C11	1N5926 B
12	1N759 A	1N963 B	BZX79C12	1N5927 B
13		1N964 B	BZX79C13	1N5928 B
14				
15		1N965 B	BZX79C15	1N5929 B
16		1N966 B	BZX79C16	1N5930 B
17				
18		1N967 B	BZX79C18	1N5931 B
19				
20		1N968 B	BZX79C20	1N5932 B
22		1N969 B	BZX79C22	1N5933 B
24		1N970 B	BZX79C24	1N5934 B
25				