

CATALOG LISTING

19HM5-CB

PAGE 1 OF 1

4

ISSUE


REVISIONS	A	201455	LJK	5 OCT 00
	B	202459	GRT	9 MAR 01
	C	0004462	KSR	APR 04
	AK			
CHECK				
25AUG00				
SAV				
CHECK				
25AUG00				
SAV				
CHECK				
25AUG00				

PTC / CAD 20

25AUG00

GJW

DRAWN



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		THIRD ANGLE PROJECTION	
ELECTRICAL DATA		SCALE 2 : 1	DO NOT SCALE PRINT
CONTACT ARRANGEMENT S P D T		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
28 VOLTS DC RATING		ONE PLACE (.0)	±.030
INDUCTIVE -- SEA LEVEL - 1/4 AMP		TWO PLACE (.00)	±.015
RESISTIVE -- SEA LEVEL - 1/2 AMP		THREE PLACE (.000)	±.005
DIELECTRIC STRENGTH		ANGLES	±
500 VRMS - 500 μA MAX LEAKAGE		WEIGHT	.014 LB MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[19HM5-CB](#)