





| REV. | DESCRIPTION                    | DATE     | APPROVED |
|------|--------------------------------|----------|----------|
| F    | Engineering Update w/o Changes | 03/01/04 | M. C.    |
|      |                                |          |          |
|      |                                |          |          |
|      |                                |          |          |




SDC SERIES



SSD SERIES



| PART NO.       |            |                | A<br>±.032 (.8) | B<br>±.016 (.4) |
|----------------|------------|----------------|-----------------|-----------------|
| SDC-250        | SSD-250    | SSD-250-102    | 2.5 (63.5)      | 1.5 (38.1)      |
| SDC-300        | SSD-300    | SSD-300-102    | 3.0 (76.2)      | 2.0 (50.8)      |
| SDC-350        | SSD-350    | SSD-350-102    | 3.5 (88.9)      | 2.5 (63.5)      |
| SDC-400        | SSD-400    | SSD-400-102    | 4.0 (101.6)     | 3.0 (76.2)      |
| N/A            | SSD-450 3X | N/A            | 4.5 (114.3)     | 3.0 (76.2)      |
| SDC-450        | SSD-450    | SSD-450-102    | 4.5 (114.3)     | 3.5 (88.9)      |
| SDC-500        | SSD-500    | SSD-500-102    | 5.0 (127.0)     | 4.0 (101.6)     |
| SDC-550        | SSD-550    | SSD-550-102    | 5.5 (139.7)     | 4.5 (114.3)     |
| SDC-600        | SSD-600    | SSD-600-102    | 6.0 (152.4)     | 5.0 (127.0)     |
| SDC-650        | SSD-650    | SSD-650-102    | 6.5 (165.1)     | 5.5 (139.7)     |
| SDC-700        | SSD-700    | SSD-700-102    | 7.0 (177.8)     | 6.0 (152.4)     |
| SDC-750        | SSD-750    | SSD-750-102    | 7.5 (190.5)     | 6.5 (165.1)     |
| SDC-800        | SSD-800    | SSD-800-102    | 8.0 (203.2)     | 7.0 (177.8)     |
| SW=0.075 (1.9) |            | SW=0.102 (2.6) |                 |                 |



2. MATERIAL: NYLON 6/6, 94V-2, NATURAL. BIVAR MATERIAL CODE 03-NL.  
BASF ULTRAMID NYLON 6/6 A3K NATURAL.
1. GENERAL SPECIFICATIONS: BIVAR MOLDED COMPONENT SPECIFICATION BV00-E101.

|                                                      |                   |                                                                            |                |
|------------------------------------------------------|-------------------|----------------------------------------------------------------------------|----------------|
| STANDARD TOLERANCE<br>( UNLESS OTHERWISE SPECIFIED ) |                   | <br>4 THOMAS, IRVINE, CA. 92618<br>TEL: (949) 951-8808 FAX: (949) 951-3974 |                |
| DECIMALS                                             | ANGULAR           |                                                                            |                |
| .X ± .1                                              | X° ± 1°           | <br>TITLE:<br>INTERCHANGEABLE SNAP-IN CARD GUIDE                           |                |
| .XX ± .01                                            |                   |                                                                            |                |
| .XXX ± .005                                          |                   | PART NO: SDC-XXX<br>SSD-XXX-XXX                                            | REVISION:<br>F |
| DESIGNED:<br>David Green                             | DATE:<br>11/26/02 | CAGE CODE : 32559                                                          | SHEET # 1 OF 1 |
| CHECKED:<br>M. Chen                                  | DATE:<br>11/26/02 | CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.                            |                |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## BIVAR:

[SDC-250](#) [SDC-300](#) [SDC-400](#) [SDC-450](#) [SDC-500](#) [SDC-600](#) [SDC-650](#) [SDC-700](#) [SDC-800](#) [SSD-800-102](#) [SSD-250](#) [SSD-600](#) [SDC-250 BK](#) [SDC-300 BK](#) [SDC-350](#) [SDC-450 BK](#) [SDC-450 VT](#) [SDC-550](#) [SDC-650 BK](#) [SDC-750](#) [SSD-250 BK](#) [SSD-300](#) [SSD-300 BK](#) [SSD-350](#) [SSD-400](#) [SSD-450](#) [SSD-550](#) [SSD-550 BK](#) [SSD-650](#) [SSD-750](#) [SSD-800](#)