

南京錠 PADLOCKS


INDUSTRIAL LOCKS



C-555-50

鍵違い
Key differences

C-555-30L/S



商品番号 Product No.	RoHS CAD	L	W ₁	W ₂	W ₃	(H)	φD	最大鍵違い数 Max. No. of key differences	コード Code	単価 Price	量販価格 Bulk Price 数量 Quantity	単価 Price
C-555-50		36	25	48	14	22	7	1300	20765	¥1,800	10個～	¥1,728
C-555-60		43	32	58	16	30	8		20767	¥2,600	5個～	¥2,496
C-555-70	2D	50	41	70	21	43	11	3200	20768	¥5,600	5個～	¥5,376
C-555-20L/S		20.5	14	20	10	47	3.5		22835	¥1,100	10個～	¥1,056
C-555-25L/S		23	17	25	10	59	4.5	24	22836	¥1,100	10個～	¥1,056
C-555-30L/S		25.5	21	31	12	71	5		22837	¥1,200	10個～	¥1,152
C-555-35L/S		25.5	25	34	12	84	5	96	22838	¥1,350	10個～	¥1,296
C-555-40L/SM		32	21	39	13.5	50	6		22839	¥1,650	10個～	¥1,584
C-555-40L/SL		32	28	39	13.5	95	6	500	22840	¥1,750	10個～	¥1,680
C-555-45L/S	2D	32	31	44	13.5	108	6		22842	¥1,950	10個～	¥1,872
C-555-50L/S		35	33	48	14	120	7	1300	22843	¥2,350	5個～	¥2,256

● : RoHS指令対応品 ▲ : RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。

C-555
黄銅製

特徴 Feature

- ワンタッチロックタイプ: 吊金を奥まで押込むと施錠されます。
- One-touch lock type: Pressing the plunger in fully will activate the lock.

仕様 ● 材質: 本体/快削黄銅棒(C3604BD)
吊金/C-555-20~60/銅合金(C2800W)
C-555-70・C-555-L/S/軟鋼線材(SWRM)

- 表面仕上: 本体/ヘアライン仕上
吊金/C-555-50~60/クリアー塗装
C-555-70・C-555-L/S/
クロムめっき(MFCr)
- 付属品: キー3本(C-555-20L/Sのみ付属キーは2本です。)

納期考備 ● 標準品...納期お問合せ下さい
● 同一鍵番号も製作致します。お問合せ下さい。
● C-555-40L/SSL、-60L/Sは中止品となりました。

Specifications ● Material: Main body: Free cutting brass bar (C3604BD)
Shackle: C-555-20~60: Brass alloy (C2800W)
C-555-70・C-555-L/S:
Soft steel wire (SWRM)

- Finish: Main body: Hairline finish
Shackle: C-555-50~60: Baked clear
C-555-70・C-555-L/S:
Chrome plating (MFCr)

- Accessories: Three keys(Only C-555-20L/S has 2 accessory keys.)

Remarks ● Products C-555-40L/SSL and -60L/S are no longer manufactured.