


Spirit Fillings; Low Range; Cases; Safety Coatings



305mm Red Spirit Filled Stirring Thermometers with white-backed glass. Stirring bulbs. Non-roll fittings. Order in tens.

Range	Division	Imm.	Product No.
-10/50C	0.5	76mm	44/401 708132-
-10/110C	1	76mm	44/403 7081332
-10/150C	1	76mm	44/406 708134

205mm Stirring. Order in tens.

-10/110C	1	76mm	44/423
----------	---	------	--------

305mm Low Range Spirit Filled Thermometers with white-backed glass.

-100/50C	1	Total	46/456
-50/50C	1	Total	46/539

380mm Low Range Thermometer. Clear pentane filled.

-200/30C	1	Total	46/440
----------	---	-------	--------

Safety Coated Laboratory Thermometers. 295mm 'Teflon'* coated mercury filled thermometers.

-20/110C	1	76mm	41/903/0
-20/150C	1	76mm	41/906/0
-10/200C	1	76mm	41/908/0
-10/250C	1	76mm	41/910/0

Slot Cases for Laboratory Thermometers. Screw caps.

Thermometer Length	Product No.
Brass	
155mm	47/732/0 7081911
205mm	47/632/0
255mm	47/532/0
305mm	47/432/0 7081900
355mm	47/832/0
405mm	47/932/0
Stainless Steel	
155mm	47/734/0
205mm	47/634/0
255mm	47/534/0
305mm	47/434/0
355mm	47/834/0
405mm	47/934/0

'Teflon'* Dupont registered trade mark