




TW-20-03-L-Q-400-085

TW-08-09-F-T-165-100

TW-16-06-T-D-500-100

TW SERIES

THROUGH-HOLE BOARD STACKERS



TW

NO. PINS PER ROW

LEAD STYLE

PLATING OPTION

ROW OPTION

STACKER HEIGHT

TAIL SPEC

02 thru 50

Specify
LEAD STYLE
from
chart below.

-F
= Gold flash
on post,
Matte Tin on tail

-L
= 10μ" (0,25 μm)
Gold on post,
Matte Tin on tail

-T
= Matte Tin

-S
= Single
Row

-D
= Double
Row

-T
= Triple
Row

-Q
= Four
Row

-5
= Five
Row

-6
= Six
Row

-“XXX”
= Stacker
Height
in inches
(0,13 mm) .005”
increments
Example: -250
= (6,35 mm)
.250”

LEAD STYLE	OAL
-01	(8,20) .323
-02	(9,60) .377
-03	(13,60) .535
-04	(14,10) .555
-05	(15,10) .594
-06	(17,10) .673
-07	(19,10) .751
-08	(21,10) .830
-09	(11,60) .456
-10	(15,60) .614
-11	(10,08) .397
-12	(28,19) 1.110

-“XXX”
= Tail Length
in inches
(0,13 mm) .005”
increments
Example: -150
= (3,81 mm)
.150”

-“XXX”
= Polarized
Position
(Specify
position to
be removed)

-S, -D*, -Q **-T, -5, -6**

* Style -08 & -12 = S & D only

ROW OPTION	STACKER HEIGHT
-S, -D*, & -Q	(3,05) .120 MIN
-T, -5, -6	(4,06) .160 MIN

* -D with stacker height greater than (4,06 mm) .160” will not have standoffs.

*-D with stacker height greater than (4,06 mm) .160" will not have standoffs.