

SL1.5X4G

Slotted Wall Wiring Duct, 1.5" X 4", Non-Adhesive, PVC, Gray, 30ft/Box

Article Number: 181-15403

Part Number: SL1.5X4G

Type: SL1.5X4

[Find a Distributor](#)

[Order Samples](#)

[Get Technical Drawings](#)

[!\[\]\(3342c215b2a8b663596a81468d5dc314_img.jpg\) \[!\\[\\]\\(5e22d44aef1f9548ca8274cbfb388e9d_img.jpg\\) \\[!\\\[\\\]\\\(b011182daf5a0527ed818f91dc4cf8f7_img.jpg\\\) | \\\[!\\\\[\\\\]\\\\(e021942709a217cfed2f781c62feb09c_img.jpg\\\\) Share\\\]\\\(#\\\)\\]\\(#\\)\]\(#\)](#)

Base Data

Part No.	SL1.5X4G
Type	SL1.5X4
Color	Light Grey (LTGY)
Features	• Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening design in the finger of the duct helps keep wires in place. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

Product Dimensions

Length (L)	6.0ft / 1.83m
Width (W) (Imperial)	1.5"
Width (W)	38.1mm
Width (W2)	1.5" / 38.1mm
Width (W3)	0.4" / 10.16mm
Width (W4)	1.0" / 25.4mm
Width (W5)	3.6" / 91.4mm
Height (H)	4.06" / 103.12mm
Mounting Hole Centers	4.00" / 101.6mm

Material and Specifications

Material	Polyvinylchloride (PVC)
CSA Certified	Yes
Flammability	self-extinguishing
Material Specification	RoHS
Operating Temperature	+122 °F (+50 °C)
Specification	UL / CSA
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes / Yes

Logistic and Packaging

Packaging Type	box
----------------	-----

Pkg. Qty.	120 / 120
Carton Qty.	120
EAN code	4031026414713
UPC	089306048107

Find a Distributor

Get Product Samples

Get Technical Drawings