








NUMBER OF POSITIONS	DIMENSION	
	A	B
06	4.0	11.2
08	6.0	13.2
10	8.0	15.2
12	10.0	17.2
14	12.0	19.2
16	14.0	21.2
18	16.0	23.2
20	18.0	25.2
22	20.0	27.2
24	22.0	29.2
26	24.0	31.2
28	26.0	33.2
30	28.0	35.2
32	30.0	37.2
34	32.0	39.2
36	34.0	41.2
38	36.0	43.2
40	38.0	45.2
44	42.0	49.2
48	46.0	53.2
50	48.0	55.2
54	52.0	59.2
56	54.0	61.2
60	58.0	65.2
62	60.0	67.2
64	62.0	69.2
68	66.0	73.2
80	78.0	85.2

MATERILA&FINISH
insulator:PBT Glass Fiber(UL94V-0)BLAKC
Contact:Brass
Contact:Gold-Plated Over Nickel
SPECIFICATIONS
Current Rating:1A AV,DC
Voltage Rating:250V AC,DC
Temperature Range:-40°C TO +150°C
Contact Resistance:20mΩ Min
Insulation Resistance:1000mΩ Min
withstanding Voltage:500V AC/Min

UNLESS OTHERWISE SPECIFIED TOLERANCE : X. ±0.20 ANGLES : ±2° X.X ±0.15 X.XX ±0.10 DO NOT SCALE DRAWING		CnC Tech ,LLC Industrial Cable and Connector Technology			
DRAWN BY		PART NO. 3130-01-XX-0104			
CHECKED BY		SIZE A	UNIT MM	TITLE 2.0/IDC	REV B0
APPROVED BY		SCALE		THIRD ANGLE PROJECTION	PAGE 1 OF 1
DWG NO.				ITEM NO.	DATE 2005/07/17