


**KEMET Part Number: PME264NE6100MR30**  
(P264EL104M660A)

Capacitor, film, 0.1 uF, +/-20% Tol, -40/+85C, Safety: X2, 660 VAC, Lead Spacing=25.4 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	30.50	MAX
H	22.00	MAX
T	15.30	MAX
S	25.40	+/-0.5
LL	30.00	+5
F	1.00	NOM

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	75

General Information	
Supplier:	KEMET
Dielectric:	Metallized Paper
Application:	Safety: X2
Style:	Radial Molded
Approvals:	ENEC,UL
RoHS:	Yes

Specifications	
Capacitance:	0.1 uF
Voltage:	1500 VDC
Tolerance:	+/-20%
Voltage AC:	660 VAC
Rated Temperature:	85C
Temperature Range:	-40/+85C
Dissipation Factor @ 1 kHz:	1.3%
Insulation Resistance:	12 GOhm
Maximum dVdT:	600 v/us