



CIRCUIT: DPDT 3-WAY
NOTE: JUMPER PIN 3 TO PIN 5

SWITCH FUNCTION			
POS. 1	POS. 2	POS. 3	
DN	DN	DN	
2-3,5-6	2-3,5-4	2-1,5-4	

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC OR 28VDC
2A @250VAC
5. MATERIALS: FIXED TERM. &MOVING CONTACT:
Cu Alloy w/Silver plate
6. ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1000V RMS @sea level
9. OPERATING TEMP.: -30°C to 85°C



9. OPERATING TEMP.: -30°C to 85°C							
A	13078	RELEASED FOR PRODUCTION	4/24/03	AR			
REV.	ECN NO.	DESCRIPTION	DATE	CHKD			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED							
TITLE				E-SWITCH®			
100DP6T1B1M2QE							
SCALE	2:1	DATE	4/24/03	DR	AR	DWG	T126063
				REV		A	