



40mm sq.**San Ace 40****General Specifications**

- Material.....Frame: Plastics (Flammability: UL94V-0),
Impeller: Plastics (Flammability: UL94V-1)
- Expected LifeRefer to specifications (L10:Survival rate:90% at 60°C ,
rated voltage, and continuously run in a free air state)
- Lead Wire⊕red ⊖black or blue (Sensor) yellow
- Storage Temperature ...-30°C to +70°C (Non-condensing)

**40×40×10**mm (Mass : 19g) **9P type****Specifications** The following nos. **have pulse sensors and ribs.**

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Airflow [m³/min] [CFM]		Max. Static Pressure [Pa] [inchH ₂ O]		SPL [dB(A)]	Operating Temperature [°C]	Expected Life [h]
109P0405H901	5	4.5 to 5.5	0.16	0.8	6,200	0.15	5.3	41.2	0.165	25	-10 to +60	40,000/60℃
109P0405M901			0.11	0.55	5,000	0.12	4.2	27	0.108	21		
109P0412H901	12	7 to 13.8	0.07	0.84	6,200	0.15	5.3	41.2	0.165	25		
109P0412M901			0.06	0.72	5,000	0.12	4.2	27	0.108	21		

Other sensor specifications are available as options. Please refer to the index (pp. 496 to 497).

Dimensions (unit: mm)**Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sanyo Denki:

[109P0405H902](#) [109P0412H902](#) [109P0412M902](#) [109P0412M9D01](#) [109P0412H9D01](#) [109P0405M902](#)
[109P0405H9D01](#) [109P0405M9D01](#)