

SFM, SFML SERIES

High-reliability
Tiger Eye™
contacts

(1.27 mm x 1.27 mm)
.050" x .050" micro pitch

OTHER SOLUTIONS

- Lower cost plating options.
See SFC Series.

Mates with TFM
for coplanar and
perpendicular mating

Surface mount or
Through-hole tails

Screw down
option




ALSO AVAILABLE (MOQ Required)

- Solder nail option
- Other sizes
- Other platings
- Contact Samtec.

PLATING OPTION

-L
= 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail
(Call Samtec for E.L.P.™ plating option)

LEAD STYLE	A	B
-01, -L1, -T1	(3.05) .120 (0.51) .020	
-03, -L3	(1.91) .075 (0.41) .016	




ROW OPTION

-S
= Single Row
(SFM only)

-D
= Double Row

-SH
= Single Horizontal
(05 thru 30 positions only)
(SFM only)
(Lead style -02 only)

-DH
= Double Horizontal
(05 thru 30 positions only)
(SFM only)
(Lead style -02 only)



OPTION

Specify only -A, -LC or -DS
(Not available with -DH, -SH)
-A
= Alignment Pin
(Available with all lead styles)

-LC
= Locking Clip
(Available with all lead styles)
(Manual placement required)

-DS
= Dual Screw Down for
(1.60 mm) .062" PCB
(05 thru 40 positions only)
(Lead styles -01, -02 & -03 only)
(Requires -D row option)
(Not available with SFML)
(Mates with TFM-DS option)
(Not available with -A,
-LC, -K, -P, -TR)


Specify only
-K or -P
(Lead styles -02,
-L2, -T2 only)

-K
= Polyimide film
Pick & Place Pad
(Not available
with -DH, -SH)

-P
= Plastic Pick &
Place Pad
(Not available
with -DH, -SH)

Specify -TR last
(Lead styles -02,
-L2, -T2 only)

-TR
= Tape & Reel
(Required callout
for -DH, -SH)



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.