


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AJ	16		A	REVISED PER EC OS14-0150-05	01JULY05	BM JL
			A1	REVISED PER ECO-09-024927	18DEC09	KK AEG



1 DIELECTRIC : DELRIN/POLYMETHYLPENTENE
PLUG CENTER CONTACT : BRASS
PLUG OUTER CONTACT : BRASS
SHELL : ZINC

2 NICKEL PLATE .000120” MINIMUM THICK

3. INTERMATEABLE WITH PRODUCT PER MIL-C-39012

4 SILVER PLATE .000200” MINIMUM THICK
OVER .000050 MINIMUM THICK NICKEL.

5 PHOSPHOR BRONZE

6 BERYLLIUM COPPER

7 BULK PACKAGED: 25 PCS PER BAG

8 BULK PACKAGED: 5 PCS PER BOX

9 INDIVIDUALLY PACKAGED

10 BULK PACKAGED: 100 PCS PER BAG.


11 INDIVIDUALLY PACKAGED FOR NETCON.

12 GOLD PLATE, .000015 MINIMUM THICK
OVER .000050 MINIMUM THICK NICKEL.

13 GOLD PLATE, .000030 MINIMUM THICK
OVER .000050 MINIMUM THICK NICKEL.

14 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

8	14	OBSOLETE	5	2	4	1-5413592-5
9	14	OBSOLETE	6	2	4	1-5413592-1
11			5	2	12	5413592-9
10			6	2	13	5413592-6
10			5	2	12	5413592-2

		MATERIAL: JACK CENTER CONTACT		SHELL PLATING		CONTACT PLATING		PART NO	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN L. VARELA — DOCK5 22APR2005 CHK J. HAVENER 22APR2005 APVD J. LIPPERT 22APR2005		Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		T-ADAPTER SERIES BNC			
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-12090 APPLICATION SPEC —		SIZE A2		CAGE CODE 00779	
MATERIAL		FINISH		WEIGHT —		DRAWING NO C-5413592		RESTRICTED TO —	
				CUSTOMER DRAWING				SCALE 2:1	
						SHEET 1 of 1		REV A1	