


LOC	DIST	P	F	REVISIONS		DATE	APPD
				ZONE	LTR		
G	86				Y	REV PER 0G3A-0561-01	07OCT02 JS MS



1 STAMP AMP 1/0C 100 275/24 APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC $\pm$ 0.20[.008] 3 PLC DEC $\pm$ - ANGLES $\pm$ -		DR 30AUG94 DK SCHRUM		AMP Incorporated Harrisburg, PA 17105-3608		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			VOLTAGE RATING: NOT APPLICABLE		MATERIAL COPPER PER ASTM B-75 ANNEALED		CHK 31AUG94 AJ KAUFMAN		NAME TERMINAL, AMPOWER, WIRE SIZE: 1/0 AWG		
FOR APPLICATION TOOLING INFORMATION			WIRE CROSS SECTIONAL AREA RANGE: 42.41-60.55mm ² [83,700-119,500] CIR MILS STRAINED		FINISH TIN PLATE 0.00381[.000150] MIN THK PER MIL-T-10727		APPD 31AUG94 RE ROSER		SIZE C 00779 C-325301		
FOR ORDER ENTRY			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		APPLICATION SPEC -		APPD 31AUG94 JL MECKLEY		SCALE 4:1 SHEET 1 OF 1		
PRODUCT INFORMATION CENTER 1-800-522-6752							PRODUCT SPEC -				
TOOLING ASSISTANCE CENTER 1-800-722-1111											
1-800-526-5142											