






LOC		DIST		P		F		ZONE		LTR		Z		REV		PER		OG3C-0104-01		DATE		APPD	
AD		0																		25SEP01		JO	



- RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
- TUBE LOADED FOR AUTOMATIC INSERTION.
- TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- SPECIAL PACKAGING.



SUPSD BY 390261-6	△	TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	5-641602-3
OBSOLETE		TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641602-5
		△	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641602-4
SUPSD BY 390261-6		TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641602-3
		△	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641602-2
SUPSD BY 390261-6		TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641602-1
		CONTACT FINISH	CONTACT MAT'L	HOUSING MATERIAL	PART NO.

				PART NO		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON : 2 PL DEC ± - 3 PL DEC ± .005 ANGLES ± 0°30'		DR	8-17-87 M.CYRUS		AMP AMP INCORPORATED Harrisburg, Pa. 17105	
		CHK	8-31-87 R.MILLER			
		APPD	9-4-87 J.LAMBERT			
MATERIAL SEE TABLE		APPD	9-4-87 J.GRAY		NAME SOCKET ASSY, DIP, LADDER, 20 POS, DIPLOMATE DL	
		PRODUCT SPEC	108-1066			
FINISH SEE TABLE		APPLICATION SPEC		SIZE	FSCM NO	DRAWING NO
		114-1049		D	00779	641602
		WEIGHT	-		SCALE	5:1