

MODEL TL-2300


International size reference: D, ER32L615

TECHNICAL DATA

(Typical values @+25°C for batteries stored for one year or less)




■ Nominal capacity @ 2 mA, to 2V	16.5 Ah
■ Rated voltage	3.6 V
■ Maximum recommended continuous current	250 mA
■ Maximum pulse current capability	500 mA
■ Weight	92.5g (3.26 oz)
■ Volume	51 cc
■ Operating temperature range	-55°C to +85°C
■ U.L. Component Recognition, MH 12193	

TADIRAN
LITHIUM
BATTERIES



AVAILABLE TERMINATIONS

SUFFIX- /S STANDARD	15-5130-21500
SUFFIX- /T SOLDER TABS	15-5130-31500



LITHIUM XTRA

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance.

Rev. B 05/03