



InstaPATCH® QUATTRO MC Male to MC Male Category 6 U/UTP  
Bundled Trunk Cable, 4-port, plenum, slate

## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	InstaPATCH® QUATTRO
<b>Product Type</b>	Copper trunk cable assembly
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Cord Length, maximum</b>	90 m   295 ft
<b>Cord Length, minimum</b>	3 m   10 ft

## Electrical Specifications

<b>ANSI/TIA Category</b>	6
<b>dc Resistance, maximum</b>	0.30 ohm
<b>Safety Voltage Rating</b>	1000 V

## Environmental Specifications

<b>Environmental Space</b>	Plenum
<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Safety Standard</b>	cETL   ETL

## General Specifications

<b>Construction Type</b>	Bundled
<b>Interface, connector A</b>	MC Male
<b>Interface, connector B</b>	MC Male
<b>Cable Type</b>	U/UTP (unshielded)
<b>Information Outlet Color</b>	Silver
<b>Interface Feature, connector A</b>	Standard
<b>Interface Feature, connector B</b>	Standard
<b>Jacket Color</b>	Slate
<b>Package Quantity</b>	1

# IQP3QPQPV4-E

---

<b>Pairs, quantity</b>	16
<b>Total Ports, quantity</b>	4

## Mechanical Specifications

<b>Conductor Type</b>	Solid
<b>Contact Plating Material</b>	Precious metals
<b>Material Type</b>	Copper alloy   Polycarbonate   Zinc
<b>Plug Insertion Life, connector A, minimum</b>	100 times
<b>Plug Insertion Life, connector B, minimum</b>	100 times
<b>Plug Retention Force, minimum</b>	133 N   30 lbf
<b>Wiring</b>	T568B

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

