











- ① MILITARY PART NO., 00779, DATE CODE, PART NO. AND AMP MARKED THIS SIDE.
- ② HOUSING MAT'L: POLYPHENYLENE SULFIDE, GST-40F PER MIL-M-24519.
- ③ CONTACT MAT'L: BRASS PER QQ-B-626.
- ④ CONTACT FINISH: .000050" [0.00127] GOLD OVER .000050" [0.00127] NICKEL IN CONTACT AREA.
- ⑤ CONTACT FINISH: .000100" [0.00254] TIN-LEAD OVER .000050" [0.00127] NICKEL
- ⑥ LETTERS INDICATING OUTSIDE ROWS AND NUMBERS INDICATING END CAVITIES (ROW C ONLY) MARKED ON THIS SURFACE.
- ⑦ NUMBERS INDICATING EVERY FIVE CAVITIES MARKED, BOTH SIDES.
- ⑧ MEETS ALL REQUIREMENTS OF MIL-C-55302.
- ⑨ LINES INDICATING EVERY FIVE CAVITIES MARKED ON MATING FACE EXCEPT END CAVITIES STARTING FROM POSN. #1.

M55302-129-08	240	IV	240	447207-8
M55302-129-07	240	III	240	447207-7
M55302-129-06	240	II	240	447207-6
M55302-129-05	240	I	240	447207-5
M55302-129-04	160	IV	240	447207-4
M55302-129-03	160	III	240	447207-3
M55302-129-02	160	II	240	447207-2
M55302-129-01	160	I	240	447207-1
MILITARY P/N	NO. OF CONTACTS	TYPE	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO. 5-4-90 C. C. THOMAS		Tycos Electronics		Tycos Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 .1/16 1 .001 2 .001 3 .001 4 .001 5 .001		NAME APPROVED PRODUCT SPEC APPLICATION SPEC		PIN HEADER ASS'Y, RIGHT ANGLE, .100	
MATERIAL 2-3		FINISH 4-5		SIZE A1		CODE 00779	
				DRAWING NO C-447207		RESTRICTED TO	
				SCALE 4:1		SHEET 1 OF 1	
				CUSTOMER DRAWING		REV C	