



10 Watt F-Series Adapter with Interchangeable AC Clips Battery Charging Adapter Meets Level V Efficiency Requirements



Features

- Folding Blades
- Constant Current for Battery Charging
- 15mm Thick with Blades Folded
- Interchangeable AC Clips
- Level V Efficiency Compliant
- No load power draw <0.15W

Applications

- Tablets
- Networking Equipment
- Personal Electronics
- Peripherals

Safety Approvals

- cUL/UL
- C-Tick
- CE
- SAA

Mechanical Characteristics

- Length: 60mm (2.36in)
- Width: 47mm (1.85in)
- Height: 15.0mm (0.59in)
- Weight: 38.5g (1.36oz)

Output Specifications

Model	DC Output Voltage			Load		Efficiency Level
	Min.	Typ.	Max.	Min.	Max.	
PSA10F-050Q	4.75V	5V	5.25V	0A	2A	V
PSA10F-050Q(D) ¹	4.75V	5V	5.25V	0A	2A	V

Notes (1): D model output to compensate for DC drops in the USB cable by 400mV at full load

PhiHong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

INPUT:**AC Input Voltage Range**

90 to 264V AC

AC Input Voltage Rating

100 to 240V AC

AC Input Frequency

47 to 63Hz

AC Input Current

0.3A RMS maximum at 120V AC

0.15A RMS maximum at 240V AC

Leakage Current

100uA maximum at 240V AC

Inrush Current

60A at 240V AC

OUTPUT:**Output Power**

10W Continuous

Efficiency

79% minimum, meets Level V Requirements

Standby Power

<150mW at 230VAC

Ripple and Noise

100mVp-p at 0A-1A load

200mVp-p at 1A-2A load

Current Limit

2.5A when less than 3V (auto-restart)

ENVIRONMENTAL:**Temperature**

Operating 0 to 40C

Non-operating -40 to +85C

Humidity 10 to 90%

EMI

FCC Class B, EN55022 Class B

Immunity

ESD: EN61000-4-2 Level 3

Radiated: EN61000-4-3 Level 2

EFT: EN61000-4-4 Level 2

Surge: EN61000-4-5 Level 3

C/T: EN61000-4-6 Level 2

PFMT: EN61000-4-8

VDT: EN61000-4-11

Harmonic: EN61000-3-2 Class A

Flicker: EN61000-3-3

Dielectric Withstand (HI-POT) Test

Primary to secondary: 3000V AC, 10mA, 60 seconds

Insulation Resistance

Primary to secondary: 500V >7M OHM

FEATURES:**Over Voltage Protection**

Auto-restart 6.3V maximum

Short Circuit Protection

Must withstand continuous short circuit

Over Temperature Protection

Auto shutdown without fault

DC Output

USB A

AC Input

US Fixed Blade folding prong

Interchangeable AC Clips (fit over US prongs)

FPBAG-H (FPE, FPK, FPS)

FPB: Brazil FPI: India

FPC: China FPK: UK

FPE: Europe FPN: Argentina

FPH: Korea FPS: Australia

(Sold Separately)

Dimension Diagram Unit: mm