




| PART NAME | SERIES 30 UPRIGHT CABINET RACK | PART No. | 30-2300 | TD | 30-2306 | REV. | 1-2-02 |
|-----------|--------------------------------|----------|---------|----|---------|------|--------|
|-----------|--------------------------------|----------|---------|----|---------|------|--------|

FINISH:  
 FRAME ASSEMBLY, DOOR, SIDES,  
 TOP CDWLS & TOP COVER \_\_\_\_\_ GRAY TEXTURE OR  
 \_\_\_\_\_ ROYAL BLUE TEXTURE  
 PANEL MOUNTING RAILS \_\_\_\_\_ SMOOTH BLACK


MATERIAL:  
 PANEL MOUNTING RAILS \_\_\_\_\_ 12 GA. STEEL  
 FRAME TOP, BASE ASSEMBLY,  
 FILLERS & VERTICAL RAILS \_\_\_\_\_ 14 GA. STEEL  
 RAIL SUPPORTS \_\_\_\_\_ 16 GA. STEEL  
 TOP CDWLS, TOP COVER & SIDES \_\_\_\_\_ 18 GA. STEEL  
 DOOR \_\_\_\_\_ 20 GA. STEEL



PANEL MOUNTING RAILS (FRONT & REAR)  
 ARE TAPPED #10-32 ON E.I.A. UNIVERSAL  
 SPACING AND ARE FULLY ADJUSTABLE.

BOTTOM PIERCED FOR MOUNTING RC-7758 CASTERS.

LOAD RATING: 1200 LBS. MAX.



| PART No. | P.S.   | A      | B      | C      | D      | E      | F      | G      | H      | J      |
|----------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 30-2300  | 21.000 | 29.625 | 29.000 | 26.875 | 18.937 | —      | —      | —      | —      | —      |
| 30-2301  | 31.500 | 40.125 | 39.500 | 37.375 | 29.437 | —      | —      | —      | —      | —      |
| 30-2302  | 42.000 | 50.625 | 50.000 | 47.875 | —      | 19.281 | 17.906 | —      | —      | —      |
| 30-2303  | 52.500 | 61.125 | 60.500 | 58.375 | —      | 24.531 | 23.156 | —      | —      | —      |
| 30-2304  | 61.250 | 69.875 | 69.250 | 67.125 | —      | 28.906 | 27.531 | —      | —      | —      |
| 30-2305  | 70.000 | 78.625 | 78.000 | 75.875 | —      | 33.281 | 31.906 | —      | —      | —      |
| 30-2306  | 78.750 | 87.375 | 86.750 | 84.625 | —      | —      | —      | 25.125 | 22.312 | 23.750 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Bud Industries:

[60-2306-RB](#) [60-2307-RB](#) [60-2305-GT](#) [60-2305-RB](#) [60-2311-GT](#) [60-2309-RB](#) [60-2304-RB](#) [60-2304-GT](#) [60-2303-](#)  
[RB](#) [60-2306-GT](#) [60-2300-GT](#) [60-2300-RB](#) [30-2302-RB](#) [60-2311-RB](#) [30-2304-RB](#) [30-2304-GT](#) [30-2306-RB](#) [30-](#)  
[2306-GT](#) [60-2308-RB](#) [30-2305-RB](#) [30-2305-GT](#) [60-2310-GT](#) [30-2301-RB](#) [60-2310-RB](#) [60-2307-GT](#) [60-2302-GT](#)  
[60-2309-GT](#) [60-2302-RB](#) [60-2308-GT](#) [30-2301-GT](#) [30-2300-RB](#) [30-2300-GT](#) [30-2302-GT](#) [60-2303-GT](#) [30-2303-GT](#)  
[30-2303-RB](#) [60-2312-GT](#) [60-2312-RB](#) [60-2301-RB](#) [60-2301-GT](#)