




4 WITHOUT CRIMP EYELET AND BOOT
BAGS WITH 100 COMPONENTS
PACKED IN ONE BOX

3.0	2.4	3.0	3.0	3.0 mm				2.4 mm				2.0 mm				0.9 mm																
-	-	1	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	FOAC CAP, PROTECTIVE (STRAP TYPE), GREEN	20												
-	-	1	1	1	1		1	1	-	-	-	-	-	-	-	-	-	-	FOAC STRAIN RELIEF, PUSH ON, GREEN 3.0 mm	19												
-	-	1	1	1	1		1	1	-	-	-	-	-	-	-	-	-	-	FOAC CRIMP EYELET OPTIMATE 3.0 mm	18												
1	-	1	1	1	1		1	1	-	-	-	-	-	-	-	-	-	-	FOAC INTERNAL BODY SC 3.0 mm	17												
1	-	1	1	1	1		1	1	-	-	-	-	-	-	-	-	-	-	FOAC SPRING COMPRESSION 3.0 mm	16												
1	1	-	-	-	-		-	-	-	-	-	-	-	-	1	1	1	1	FOAC CAP PROTECTIVE, (NO STRAP), BLACK	15												
-	-	-	-	-	-		-	-	-	-	-	-	-	-	1	1	1	1	BOOT, BARE BUFFER, BEND LIMITING, GREEN	14												
-	-	-	-	-	-		-	-	-	-	-	1	1	1	1	-	-	-	FOAC BOOT 2.0 mm, GREEN	13												
-	-	-	-	-	-		-	-	-	-	-	1	1	1	1	-	-	-	FOAC CRIMP EYELET 2.0 mm	12												
-	-	-	-	1	1	1	1	1	1	1	1	1	1	1	-	-	-	-	FOAC CAP, PROTECTIVE (STRAP TYPE), BLACK	11												
-	-	-	-	-	-	-	-	-	1	1	1	1	1	-	-	-	-	-	FOAC STRAIN RELIEF, PUSH ON, GREEN 2.4 mm	10												
-	-	-	-	-	-	-	-	-	1	1	1	1	-	-	-	-	-	-	CRIMP EYELET OPTIMATE 2.4 mm	9												
-	1	-	-	-	-	-	-	-	1	1	1	1	1	1	1	1	1	1	FOAC INTERNAL BODY SC 2.4 mm	8												
-	1	-	-	-	-	-	-	-	1	1	1	1	1	1	1	1	1	1	FOAC SPRING COMPRESSION 2.4 mm	7												
-	-	-	-	-	1	-	-	-	1	-	-	-	-	-	1	-	-	-	FOAC FERR. SUBASSY SC SM 0.126/1.3	6												
-	-	1	-	-	-	1	-	-	-	1	-	-	-	-	-	1	-	-	FOAC FERR. SUBASSY SC SM 0.126/1.1	5												
-	-	-	-	-	-	1	-	-	-	-	1	-	-	-	-	-	1	-	FOAC FERR. SUBASSY SC SM 0.125/1.3	4												
1	1	-	1	-	-	-	1	-	-	-	1	-	-	-	-	-	-	1	FOAC FERR. SUBASSY SC SM 0.125/1.1	3												
1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	FOAC PLUG BODY SC GREY	2												
1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	FOAC CONNECTOR HOUSING AMP SC1 GREEN	1												
QTY	QTY	QTY	QTY	QTY	QTY		QTY	QTY		QTY	QTY		QTY	QTY		QTY	QTY		DESCRIPTION	ITEM												
9-5106785-3 	9-5106785-2 	8-5106785-1 	7-5106785-8 		3-5106785-2	3-5106785-1		2-5106785-9	2-5106785-8		5106785-8	5106785-7		5106785-5	5106785-4		3-5106785-8	3-5106785-7		3-5106785-5	3-5106785-4		2-5106785-0	1-5106785-9		1-5106785-7	1-5106785-6		THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC + - 1 PLC + - 2 PLC + - 3 PLC + - 4 PLC + - ANGLES ± - MATERIAL - DWN J.W. RIETVELD 31MAY1995 CHK A. HENGELMOLEN 29JUL2004 APVD A. HENGELMOLEN 29JUL2004 PRODUCT SPEC APPLICATION SPEC WEIGHT - CUSTOMER DRAWING Tyco Electronics Corporation 's-Hertogenbosch, Nederland NAME SIZE CAGE CODE DRAWING NO RESTRICTED TO A200779C=5106785- SCALE NTS SHEET 1 of 1 REV			