


mm (inches)



LEAD FREE P/N
86094647113785FHLF

component side

32₃₁ DIM. B 2₁

5.08 (±.000) 2.54 (±.100)

ø0.05

2.54 ±0.1 (±.100)

5.3 ±0.1 (±.200)

ø2.8 ±0.1 (±.112)

ø0.1

88.9 (3.500)

78.74 (3.100)

31 × 2.54 = 78.74 (3.100)


U

0.1 U

SEE DRAWING C-8609-0000A

ROW a : 4 Grounding pins in Cavities 1 / 10 / 30-31

[illegible]

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		mm 	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	ROUILLARD	2000/11/20	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 1.5		
Eng	TARON	2000/11/20			0.XX	±0.1				
Chr	LEGARE	2000/11/20			0.XX* ±2°	±0.1				
Appr	LEGARE	2000/11/20	Product family			DIN 8609		Spec ref -		
			RIGHT ANGLE MALE - STYLE C				dwg no C-8609-1224		Rev.	
			SOLDER TO BOARD						A	
catalog no			SEE TABLE				CUSTOMER		sheet 1 of 1	