


LOC	DIST	REVISIONS				DAP		
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
G	14		A1	REVISED PER ECR 10-010105	25JUN10	JR	TM	



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
16-14 AWG STRANDED	16-14 AWG STRANDED	NOT CERTIFIED

- 1 STAMP 10S AMP 16-14* APPROX AS SHOWN
10S INDICATES STUD SIZE
- 2 PHOSPHOR BRONZE PER ASTM B-103, ANNEALED
- 3 0.00254 [.000100] MIN TIN PLATE
PER ASTM B-545

52705-1

PART NO.

CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN TA BRINKMAN 2-16-93		Tyco Electronics Corporation Harrisburg, PA 17105-3608		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: --		DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK DA PATTERSON 2-16-93	APVD JL MECKLEY 2-16-93	PRODUCT SPEC -	NAME TERMINAL, LONG SPRING SPADE, BUDGET -		
	FOR APPLICATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED							APPLICATION SPEC -	SIZE A2	CAGE CODE 00779
TOOLING INFORMATION	1-800-722-1111			MATERIAL -	FINISH -	WEIGHT -	CUSTOMER DRAWING			SCALE 10:1	SHEET 1 of 1	REV A1
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.								