





1. FINISH : PLATE 0.000100-0.000200 THK TIN IN LOCALIZED TIN PLATE AREA, ALL OVER 0.000040-0.000080 THK NICKEL.
2. CONTACT WILL BE LUBED WITH LUBRICANT PER P/N 22014-4.
3. WIRE RANGE: 20-18 AWG WITH INSULATION DIAMETERS OF 0.089 - 0.131 INCHES.
4. PLATE 0.000030 MIN THK SELECT GOLD IN LOCALIZED PLATE AREA.



1	776349-3
1 4	776349-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. YEAGER	22FEB00	TE TE Connectivity		
DIMENSIONS: INCHES		CHK W. LONG	22FEB00			
		APVD W. LONG	22FEB00	NAME PIN CONTACT		
		PRODUCT SPEC				
MATERIAL 0.014 THK.CU.ALLOY		APPLICATION SPEC		SIZE A2	CAGE CODE 00779	DRAWING NO C=776349
		FINISH -		WEIGHT -	RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 10:1	SHEET 1 of 1	REV C2