

INTERCONNECTS

SERIES 326 • .100" GRID WRAPOST WITH SOLDER TAIL • SINGLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3

- Wrapost / Solder Tail combinations are available in 3 lengths using MM pin numbers:

326...001 uses pin # 2601

326...002 uses pin # 2602

326...003 uses pin # 2603

See page 199 for details

- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details

- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 326...001	1 Level Wrapost
	326-XX-1	-41-001000 Specify number of pins 01-64
FIG. 2	Series 326...002	2 Level Wrapost
	326-XX-1	-41-002000 Specify number of pins 01-64
FIG. 3	Series 326...003	3 Level Wrapost
	326-XX-1	-41-003000 Specify number of pins 01-64



XX=Plating Code
See Below

For
Electrical, Mechanical
& Environmental Data,
See page 264

SPECIFY PLATING CODE XX=	91	93	41	43
Sleeve (Pin)	200 μ " Sn/Pb	200 μ " Sn/Pb	200 μ " Sn	200 μ " Sn
Contact (Clip)	10 μ " Au	30 μ " Au	10 μ " Au	30 μ " Au



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[326-93-164-41-003000](#) [326-93-164-41-002000](#) [326-93-164-41-001000](#) [326-93-132-41-003000](#) [326-93-132-41-002000](#) [326-93-132-41-001000](#) [326-93-120-41-003000](#) [326-93-120-41-002000](#) [326-93-120-41-001000](#) [326-13-164-41-002000](#) [326-13-109-41-003000](#) [326-43-164-41-003000](#) [326-43-164-41-002000](#) [326-43-164-41-001000](#) [326-43-132-41-003000](#) [326-43-132-41-002000](#) [326-43-132-41-001000](#) [326-43-120-41-003000](#) [326-43-120-41-002000](#) [326-43-120-41-001000](#) [326-43-125-41-001000](#)