


15 Ampere, 125, 125/250 Volts Midget Twist-Lock Connector Bodies and Flanged Receptacles



IP20
SUITABILITY



Connector Bodies

Description	Cord Dia.	Catalog Numbers		
Valise® connector body, black nylon, polarized.	.220"-.385" (5.6-9.8)	HBL7464V	—	—
Valise® connector body, black nylon, insulation displacement terminals.	.300"-.430" (7.6-10.9)	—	HBL7593V	—
Black nylon cover, phenolic body, screw terminals.	.281"-.421" (7.1-10.7)	—	HBL7593	—
Angle connector body, black nylon cover, phenolic body, screw terminals.	.335"-.421" (8.5-10.7)	—	HBL7571	—
Valise® type, black nylon, with insulation displacement terminals, multiple drive screws.	.300"-.430" (7.6-10.9)	—	—	HBL7484V
Black nylon body, phenolic base, multiple drive screws, cord grip.	.281"-.421" (7.1-10.7)	—	—	HBL7484
Same as above, except for angle cord grip.	.335"-.421" (8.5-10.7)	—	—	HBL7433

Accessories on page B-6.

Flanged Receptacles


Description	Catalog Numbers		
Stainless steel flange, exposed terminals.	HBL7468	—	—
Exposed terminals, black nylon flange.	—	HBL7596N	—
Exposed terminals, stainless steel flange.	—	HBL7596	—
Covered terminals, stainless steel flange, accepts cord .500" (12.7) in dia.	—	HBL7598	—
Exposed terminals, black nylon flange.	—	—	HBL7487N
Exposed terminals, stainless steel flange.	—	—	HBL7487
Covered terminals, stainless steel flange, accepts cord .500" (12.7) in diameter.	—	—	HBL7489

Accessories on page B-6.

Notes: Male ML-2R devices have solid center ground pins.
Male ML-3R devices have hollow center neutral sleeves.



HBL7464V




HBL7593V



HBL7593




HBL7571



HBL7484V




HBL7484




HBL7596



HBL7598



HBL7596N



HBL7468