

Power module - EMD-SL-PS45-110AC - 2885281

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Power modules, pluggable, for EMD-FL-..., supply voltage: 88 V AC ... 121 V AC

Your advantages

- ✓ Variable supply voltage range
- ✓ Adjustable asymmetry
- ✓ Adjustable via potentiometer on the front
- ✓ Adjustable response delay

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 996529
GTIN	4017918996529
Weight per Piece (excluding packing)	94.100 g
Custom tariff number	85043180
Country of origin	Germany

Technical data

Dimensions

Width	32 mm
Height	35 mm
Depth	26 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
---------------------------------	------------------

Power module - EMD-SL-PS45-110AC - 2885281

Technical data

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 70 °C
---	------------------

Input data

Nominal input voltage	110 V AC (50/60 Hz)
-----------------------	---------------------

General

Housing material	Plastic
------------------	---------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.0	27049002
eCl@ss 5.1	27049200
eCl@ss 6.0	27049000
eCl@ss 7.0	27049002
eCl@ss 8.0	27049002
eCl@ss 9.0	27040701

ETIM

ETIM 4.0	EC002540
ETIM 5.0	EC002540
ETIM 6.0	EC002540
ETIM 7.0	EC002540

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121535
UNSPSC 11	39121535
UNSPSC 12.01	39121535
UNSPSC 13.2	39121004
UNSPSC 19.0	39121004

Approvals

Approvals

Power module - EMD-SL-PS45-110AC - 2885281

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU *- DE.**08.B-02133
-----	---	--------------------------
