





Copyright FCI.


C

D

- NOTES :
- 1- MATERIALS :
BODY : High Temp thermoplastic 30% GF, COLOR BLACK UL94 V-0
PIN : COPPER ALLOY
- 2- 7N MIN PIN RETENTION IN EITHER DIRECTION
- 3- RoHS COMPATIBLE PRODUCT SPECIFICATION :
a- PLATING : LF means the product is Lead Free,
2µ MIN matte Tin over 1.27µ Nickel underplating.
b- MANUFACTURING PRODUCT SPECIFICATION :
Housing will withstand exposure to 260°C peak temperature
for 30 secondes in a convection infra-red or vapor phase oven.
c- LABELLING :
Meets packaging specs as per GS-14-920
d- LEGAL STATMENT : See GS-47-0004
- 4- PLANE REFERENCE -A- IS GENERATED BY LONG PINS TAIL ROW
WITH LOWEST AREA OF BODY.
SHORT PINS ROW TO BE FLUSH OR HIGHER 0.1 MAX ABOVE REF -A-.
- 5- MINIMUM QUANTITY IN BLI BOX : 500



SCALE 3:1
VIEW WITH
PICK-UP CAP



spec ref	GS-12-652		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED		
ISO 406	linear	0.X	±0.30
ISO 1101		0.XX	±0.13
		0.XXX	±0.05
surface	angular	0°	±1°
ISO 1302			



www.fci.com

dr A Parrenin 2014/02/28
eng A Parrenin 2014/03/19
chr D Convercey 2014/03/20
appr Gert Dreesbeke 2014/03/21



projection
mm
product family

title
HEADER UNSHROUDED SMT
DOUBLE ROW R/A

cat. no.

size	A3	scale	4:1
ecn no	ELX-B-17245-1		
rel level	Released		
dwg no	10112690C		
rev	E		

Product - Customer Drw sheet 1 of 1



10112690 - X XX-YY Z LF

INDICATES THAT PRODUCT
IS RoHS COMPATIBLE SEE NOTE 3

PACKAGING :

A = Tape and reel with Pick-up cap
See GS-14-1516 As available
U = Tube without Pick-up cap. Only
for rows contacts qty from 4 to 25
See GS-14-1551
Blank = Bli box for rows contacts qty
2 and 3 see note 5

NBR CONTACTS PER ROW : 02 TO 25 = N

STYLE	01	02	03	04	05
DIM C POST LENGTH	3.2	2.0	4.0	7.0	5.84

PLATING : G= 0.76µ Gold/GXT on mating area
2-6µ Pure Tin on solder area
F= Gold flash on mating area
2-6µ pure Tin on solder area
T= 2-6µ pure Tin on mating area
2-6µ pure Tin on solder area
All with 1.27 Ni underplating