



LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14					D REV PER 0G3A-0012-02	21 JAN02	JR/MS



AMP WIRE RANGE	UL E13288 Listed
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED
CS LR7189 Certified	MILITARY P/N AND CLASS
12-10 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS
- 3 PRELIMINARY - NOT FOR RPRODUCTION



5,000			ON TAPE, REEL		2-324893-2	
-			LOOSE PIECE		324893	
QTY			PACKAGE TYPE		PART NO	
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± - MATERIAL COPPER PER ASTM B-152 ANNEALED	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			VOLTAGE RATING: NOT APPLICABLE		FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM B 545	
PRODUCT INFORMATION CENTER 1-800-522-6752			WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm² [5,180-13,100] CIR MILS SOLID OR STRANDED		DR 4-14-93 TA BRINKMAN CHK 4-14-93 DA PATTERSON APPD 4-14-93 DE MILLER APPD 4-14-93 JL MECKLEY PRODUCT SPEC -	
TOOLING ASSISTANCE CENTER 1-800-722-1111			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		APPLICATION SPEC -	
1-800-526-5142					WEIGHT -	
					AMP Incorporated Harrisburg, PA 17105-3608	
					NAME SPLICE, BUTT, STRAP, SOLISTRAND	
					SIZE C 00779	
					DRAWING NO C-324893	
					SCALE 10:1	
					SHEET 1 OF 1	