

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130050-0122](#)
Status: **Active**
Overview: [industrial_ethernet_solutions](#)
Description: Brad® RJ-Lnxx™ RJ-45 Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), Shielded Cable, 1.0m (3.28') Length , 26 AWG

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	130050
Connector End A	RJ-45 (industrial)
Connector End B	RJ-45 (industrial)
IP Rating	IP67
Overview	industrial_ethernet_solutions
Performance Category	5e
Product Name	Brad®, RJ-Lnxx®
Protocol	Ethernet
Region	America, Asia, Europe
Type	Double Ended
UPC	78678849687

Physical

Cable Diameter	7.37mm (.290")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Male
Keyway	None
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	ABS
Material - Plating Mating	N/A
Net Weight	5.260/g
Orientation	Straight
Poles	8
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	26
Wire/Cable Type	Shielded-Twisted Pair

Electrical


Current - Maximum per Contact	1.5A
Voltage - Maximum	125V DC

Material Info

Old Part Number	ENP2115M010
-----------------	-------------

Reference - Drawing Numbers

Sales Drawing	SD-130050-018
---------------	---------------



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[130050Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[130050-0122](#)