







Twist-Lock® Devices

15 Ampere, 125, 125/250 Volts
Midget Twist-Lock Plugs and Flanged Inlets
**HBL7465V****HBL7594V****HBL7594****HBL7570****HBL7466, HBL7467****HBL7595N****HBL7595****HBL7486N****HBL7486**
IP20
 SUITABILITY


Plugs

Description	Cord Dia.	Catalog Numbers		
Valise® plug, black nylon.	.220"-.385" (5.6-9.8)	HBL7465V	-	-
Valise® plug, black nylon, insulation displacement terminals.	.300"-.430" (7.6-10.9)	-	HBL7594V	-
Black nylon cover, phenolic body, multiple drive screw terminals.	.281"-.421" (7.1-10.7)	-	HBL7594	-
Angle plug, black nylon cover, phenolic body, multiple drive screw terminals.	.335"-.421" (8.5-10.7)	-	HBL7570	-
Valise® plug, black nylon, with insulation displacement terminals, multiple drive screws.	.300"-.430" (7.6-10.9)	-	-	HBL7485V
Black nylon body, phenolic base, multiple drive screw terminals, cord grip.	.281"-.421" (7.1-10.7)	-	-	HBL7485
Same as above, except angle cord grip.	.335"-.421" (8.5-10.7)	-	-	HBL7432

Accessories on page B-6.

Flanged Inlets

Description	Catalog Numbers		
Stainless steel flange, polarized, exposed terminals.	HBL7467	-	-
Stainless steel flange, not polarized, exposed terminals.	HBL7466	-	-
Exposed terminals, black nylon flange.	-	HBL7595N	-
Exposed terminals, stainless steel flange.	-	HBL7595	-
Covered terminals, stainless steel flange, accepts cord .500" (12.7) dia.	-	HBL7551	-
Exposed terminals, black nylon flange.	-	-	HBL7486N
Exposed terminals, stainless steel flange.	-	-	HBL7486

Accessories on page B-6.

Notes: Male ML-2P devices have hollow center ground sleeves.
Male ML-3P devices have solid center neutral pins.