



REV.	DATE	DESCRIPTION
A	02/09/05	MODIFY INTERNAL DIMENSIONS / UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



9	HEX NUT	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex							
8	WASHER	BRASS	NICKEL	1		DRAWN	G.R.S.	02/09/05									
7	GASKET	SILICONE	RED	1		CHECKED			PART DESCRIPTION								
6	BRAID CLAMP	BRASS	NICKEL	1		ISSUED			BNC CLAMP PLUG (FOR RG-58/U, 142A/U, 223/U)								
5	RING	BRASS	NICKEL	1		SHEET	1 OF 1		PART NO.								
4	INSULATOR	DELFIN	NATURAL	1					112332								
3	CONTACT PIN	BRASS	GOLD	1			CAD FILE		DWG. NO.		112332.DWG	REV.	A	SIZE	A	SCALE	NA
2	INSULATOR	DELFIN	NATURAL	1			C:/112/112332.DWG										
1	BODY	BRASS	NICKEL	1													
	DESCRIPTION	MATERIAL	FINISH	QTY													